



Product designation Power distribution block

Electrical features

Number of poles	4
Rated insulation voltage U_i	V 500
IEC Conventional free air thermal current I_{th}	A 125
Rated peak withstand current I_{pk}	kA 20
Rated short time current I_{cw} 60s	A 4.5

Connections

Terminal hole diameter_Option 1	mm	1x9mm
Conductor section connectable_Option 1	mm ²	10...35
Terminal hole diameter_Option 2	mm	3x7,5mm
Conductor section connectable_Option 2	mm ²	10...25
Terminal hole diameter_Option 3	mm	11x5,5mm
Conductor section connectable_Option 3	mm ²	2,5...6


Mechanical features

Operating position	normal allowable	Vertical plane Any
Fixing		Screw / DIN rail 35mm
Phillips		2
Weight	g	515

Resistance & Protection

Terminals IP degree	IP20 front
---------------------	------------

Dimensions



Certifications and compliance

Certifications

IEC/EN/BS 60947-7-1

ETIM classification

EC000066 - Power contactor, AC switching

□