




Product designation	Power distribution block	
Electrical features		
Number of poles		4
Rated insulation voltage Ui	V	500
IEC Conventional free air thermal current Ith	A	160
Rated peak withstand current Ipk	kA	38
Rated short time current Icw 60s	A	8.2
Connections		
Terminal hole diameter_Option 1	mm	1x11,5
Conductor section connectable_Option 1	mm2	10...50
Terminal hole diameter_Option 2	mm	3x8,5mm
Conductor section connectable_Option 2	mm2	10...25
Terminal hole diameter_Option 3	mm	8x7mm
Conductor section connectable_Option 3	mm2	2,5...16
Mechanical features		
Operating position	normal allowable	Vertical plane Any
Fixing		Screw / DIN rail 35mm
Phillips		2
Weight	g	615
Resistance & Protection		
Terminals IP degree		IP20 front
Dimensions		



Certifications and compliance

Certifications

IEC/EN/BS 60947-7-1

ETIM classification

EC000066 - Power contactor, AC switching

□