



Product designation			Protocol converter	
Product type designation			EXCCON02	
General characteristics				
Description			RS485-Ethernet Modbus protocol converter	
Functions			RS485/Ethernet	
Rated power supply voltage			9...48VDC, 24VAC	
Communications				
Type of communication port			RS485/Ethernet	
Protocols supported			Modbus, Serial device TCP server/client	
Monitoring method				
Transmission technology			Ethernet/TCP	
Device setup and supervision			Webserver	
Interface				
RS232 communication			Yes	
RS485 communication			Yes	
Ethernet communication			Yes	
Mobile communication			No	
Mechanical features				
Fixing			DIN rail or rear mounting	
Weight		g	430	
Ambient conditions				
Temperature				
Operating temperature			min	°C
			max	°C
			-40	
			+75	
Certifications and compliance				
Certifications				
			IEC/EN/BS 55024	
			IEC/EN/BS 55032	
			IEC/EN/BS 55035	
Compliance				
			EAC	
			UCKA	
ETIM classification				
EC000066 - Power contactor, AC switching				