




Product designation			Push-push button actuators	
Product type designation			LPCQ10	
General characteristics				
Colour			Yellow	
Type of positions			Flush pushbutton. Push on-push off	
Material			Polyamide	
IEC degree of protection			IP66, IP67 and IP69K	
Mechanical features				
Operating force		kg-lb	<0.5Kg / 1.1lb	
Mechanical life - Push-Push actuators		cycles	500000	
Fixing		Without mounting adapter		
Mounting adapter		LPXC10A (1EM) / LPXC01 (1NC)		
Weight		g	25	
UL technical data				
UL degree of protection		Type1, 2, 3R, 4, 4X, 12, 12K		
Ambient conditions				
Temperature				
Operating temperature		min	°C	-25
		max	°C	+70
Storage temperature		min	°C	-40
		max	°C	+85

Dimensions



Certifications and compliance

Compliance

CSA C22.2 n° 14
IEC/EN/BS 60947-1
IEC/EN/BS 60947-5-1

Certificates

UL508

CCC

cULus

EAC

RINA

ETIM classification

ETIM 8.0

EC000221 -
Front element for
push button