



Adapter for  
Ø30mm/1.18"  
holes to  
Ø22mm/0.87"  
LPXA162M

Product designation

Product type designation

### Ambient conditions

Temperature

Operating temperature

min	°C	-25
max	°C	+70

Storage temperature

min	°C	-40
max	°C	+85

### Certifications and compliance

Compliance

/

Certificates

cULus

### ETIM classification

ETIM 8.0

EC002498 -  
Accessories/spare  
parts for low-  
voltage switch  
technology