



Product designation

Reversing
contactor
BGTP09

Product type designation

Electrical features

Maximum operating current ($\leq 440V$) A 9

Contact characteristics

Operational current I_e AC-3 ($\leq 440V \leq 55^\circ C$) A 9

Rated operational power AC-3 ($T \leq 55^\circ C$)

230V	kW	2.2
400V	kW	4
415V	kW	4.3
440V	kW	4.5
500V	kW	5

Built-in auxiliary contacts

NO	0
NC	1

UL technical data

Maximum UL/CSA horsepower ratings single-phase

110V-120V	HP	0.5
220V-240V	HP	1.5

Maximum UL/CSA horsepower ratings three-phase, 3-pole


200V-208V	HP	2
220V-240V	HP	3
440V-480V	HP	5

Mechanical features


Terminals type Clamp screw

Weight g 400

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 60947-1

IEC/EN 60947-4-1

UL508 CSA C22.2 n° 14

Certificates

cULus

ETIM classification

ETIM 8.0

EC001037 -
Motor
starter/Motor
starter
combination