




Product designation			Current transformers	
Product type designation			DM1TMA0200	
Type of CT			Split-core	
Current inputs				
Primary current I _{pn} (/5)			A	200
Operational frequency			min	Hz
			max	Hz
Secondary output current			A	5
Overload withstand I _{pn}			%	120
Burden			cl. 1	VA
Insulations				
Rated insulation voltage U _i IEC/EN			V	720
IEC rated short-time thermal current I _{th}			I _{th} for s	40...60
IEC rated dynamic current I _{dyn}			I _{th} for s	2.5
Insulation dry type			Class E	
Mechanical features				
Terminals type			2m pre-wired	
Weight			g	200
Ambient conditions				
Temperature				
Operating temperature			min	°C
			max	°C
Storage temperature			min	°C
			max	°C
Relative humidity			%	90
Dimensions				



Certifications and compliance

Certifications

IEC/EN/BS 61869-1

IEC/EN/BS 61869-2

Compliance

EAC

ETIM classification

EC000066 - Power contactor, AC switching