



Product designation

Direct-on-line
starter

Product type designation

M0R00912...1

Electrical features

Relay adj range	A	0.6-1
IEC technical characteristics ($\leq 440V$)	le kW	A kW
	1	0.18...0.25

Components

Starter enclosure standard supplied	M0RA
Contactor standard supplied	BG0910A
Thermal relay standard supplied	RF91

Mechanical features

Weight	g	720
--------	---	-----


Ambient conditions

Operating temperature	min max	°C °C	-25 +60
Storage temperature	min max	°C °C	-40 +70


Resistance & Protection

Frontal IP degree	IP65
-------------------	------

Dimensions



Wiring diagrams



R = Reset; I = Start; O = Stop

Certifications and compliance

Compliance

IEC/EN 60947-1
IEC/EN 60947-4-1
UL508 CSA C22.2 n° 14

Certificates

CSAus
cULus
EAC

ETIM classification

ETIM 8.0

EC001037 -
Motor
starter/Motor
starter
combination