



|                          |              |
|--------------------------|--------------|
| Product designation      | Fuse 10x85mm |
| Product type designation | FE           |
| Operating voltage type   | DC           |

#### Electrical features

|                                |     |      |
|--------------------------------|-----|------|
| IEC maximum rated current (In) | A   | 15   |
| IEC maximum rated voltage (Un) | V   | 1500 |
| Rated current (In)             | A   | 15   |
| IEC fuse class                 |     | gPV  |
| Power consumption at 0,7 In    | W   | 1.9  |
| Power consumption at In        | W   | 2.7  |
| Prearcing I2t                  | A2s | 171  |
| Total I2t at 1000Vdc           | A2s | 295  |


#### Ambient conditions

|                       |     |    |      |
|-----------------------|-----|----|------|
| Operating temperature | min | °C | -20  |
|                       | max | °C | +70  |
| Storage temperature   | min | °C | -40  |
|                       | max | °C | +80  |
| Max altitude          | m   |    | 3000 |

#### Mechanical features

|        |   |    |
|--------|---|----|
| Weight | g | 19 |
|--------|---|----|

#### Dimensions



#### Certifications and compliance

|            |                   |
|------------|-------------------|
| Compliance | IEC/EN/BS 60269-6 |
|------------|-------------------|

#### ETIM classification

|          |                                |
|----------|--------------------------------|
| ETIM 8.0 | EC002704 -<br>Cylindrical fuse |
|----------|--------------------------------|