





Product designation		AMF controller
Product type designation		RGK900
Power supply		
Rated battery voltage	V	12/24VDC
Digital inputs		
Digital input type		12 neg.+ 1 pos.
High digital input signal	V	See eBOM
"W"/AC/PICK-UP speed inputs		
"W"/AC/PICK-UP speed input type		"W" or generator frequency or "Pick-up"
Voltage inputs		
Rated voltage (Ue)	VAC	100...600
Measurement range	V	30...720
Frequency range	Hz	45...65 or 360...440
Measurement method		TRMS
Current inputs		
Rated current (Ie)	A	5A/1A
Measurement range		0.05...6A or 0.05...1.2A
Amperometric inputs type		3PH, /5A or /1A
Measurement method		TRMS
Static Outputs		
Static output type		6 (SSR) + 1 (SO)
Rating	A	2
Protections		Protected
Relay outputs		
Type of output contact		3 (relay)
Rated current at 250V in AC-1	A	8
Interface		
CANbus		Yes
Ambient conditions		
Protection degree		IP65
Dimensions		



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 14

IEC/EN 61000-6-2

IEC/EN 61000-6-3

IEC/EN 61010-1

UL 508

Certificates

EAC

UL Listed for USA and Canada (cULus-File E93601)

ETIM classification

ETIM 8.0

EC002758 -
Energy
management
controller