



Enclosed automatic transfer switches ATS, with ATL600 controller and four-pole contactors, 125A ATP

Product designation

Product type designation

General characteristics

Number of controlled power sources	Nr.	2
Display		Backlit LCD graphic display 128x80 pixel
Languages	Nr.	5
AC Power supply		
Rated frequency	Hz	50/60
Operating frequency range	Hz	45...65
Immunity time for microbreakings	220VAC ms	≤250

Voltage inputs

Maximum rated voltage U_e		400
Frequency range	Hz	45...65
Measurement method		True root mean square (TRMS)

Current inputs

Rated current (I_e)	A	125 (AC1)
-------------------------	---	-----------

Digital inputs

Number of digital input	Nr.	6
-------------------------	-----	---

Relay outputs

Number of relay output	Nr.	7
Contact arrangement		6 x 1NO-SPST + 1 x C/O-SPDT
Electrical life	cycles	10^5
Mechanical life	cycles	10^7

Interface

Front optical USB communication port		Yes, with CX01 USB dongle (optional)
Front optical Wi-Fi communication port		Yes, with CX02 Wi-Fi dongle (optional)

Insulations

Voltage inputs		
	Rated insulation voltage U_i	VAC 400
	Rated impulse withstand voltage U_{imp}	kV 4


Ambient conditions

Maximum Pollution degree	2
Overvoltage category	3

Housing


Material	Metallic
Degree of protection	IP65
Dimensions (W x H x D)	mm 600 x 400 x 250

Dimensions



Wiring diagrams

AUTOMATICKÁ JEDNOTKA ŘÍZENÍ ZÁSKOKŮ SÍTÍ V KOVOVÉM KRYTU ATS, NAPÁJENÍ 230VAC, SE STYKAČI VE ČTYŘPÓLOVÉM PROVEDENÍ, PROVOZNÍ PROUD 125 A, VÝKON (400 V) 87 KVA, ROZMĚRY (600X400X250MM)



Certifications and compliance

Compliance

IEC 61439-2