





Product designation	Automatic mains failure gen-set controllers	
Product type designation	RGK750	
Power supply		
Rated battery voltage	V	12/24VDC
Digital inputs		
Digital input type	8 neg.+ 1 pos.	
"W"/AC/PICK-UP speed inputs		
"W"/AC/PICK-UP speed input type	"W" or generator frequency or "Pick-up"	
Voltage inputs		
Rated voltage (Ue)	VAC	100...480
Measurement range	V	100...480
Frequency range	Hz	45...65
Measurement method	TRMS	
Current inputs		
Rated current (Ie)	A	5A/1A
Measurement range	0.05...6A or 0.05...1.2A	
Amperometric inputs type	3PH, /5A or /1A	
Measurement method	TRMS	
Static Outputs		
Static output type	6 (SSR) + 1 (SO)	
Relay outputs		
Type of output contact	3 (relay)	
Interface		
CANbus	Yes	
Ambient conditions		
Protection degree	IP65	
Dimensions		

JEDNOTKY ŘÍZENÍ ZÁLOŽNÍCH MOTOR-GENERÁTORŮ, 12/24VDC, GRAFICKÝ LCD
DISPLEJ, USB/OPTICKÝ A WI-FI PORT NA PŘEDKU PRO PROGRAMOVÁNÍ, PORT CANBUS,
8 VSTUPŮ, 10 VÝSTUPŮ, ROZŠÍŘITELNÉ POMOCÍ EXP ...



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 61000-6-2

IEC/EN 61000-6-3

IEC/EN 61010-1

Certificates

EAC

ETIM classification

ETIM 8.0

EC002758 -
Energy
management
controller