



RJ45 interface,
Ethernet
connection type
LPCD0
Cat.5E

Product designation

Product type designation

Transmission characteristics

General characteristics

Material	Polyamide
IEC degree of protection	IP65 on front and IP20 on rear

Electrical characteristics

Rated insulation voltage U_i IEC/EN	V	24VAC
Contact resistance	mΩ	≤40

Mechanical features

Weight	g	26
--------	---	----


UL technical data

UL degree of protection	1, 2, 3R, 4, 4X, 12, 12K on front
-------------------------	--------------------------------------

Ambient conditions

Temperature			
Operating temperature	min	°C	-25
	max	°C	+70
Storage temperature	min	°C	-40
	max	°C	+85

Dimensions



Certifications and compliance

Compliance	CSA C22.2 n° 14
	IEC/EN/BS 60947-1
	IEC/EN/BS 60947-5-1
	UL508
Certificates	cULus
	EAC

ETIM classification

ETIM 8.0	EC002780 - Interface module
----------	--------------------------------