



Signal tower
Ø70mm/2.75"
8TL7EL - Light
modules

Product designation

Product type designation

General characteristics

Diameter	mm - inch	70 / 2.75
Supply voltage (DC)	V	24
Colour		Orange
IEC degree of protection		IP65


Mechanical features

Weight	g	82
--------	---	----


Ambient conditions

Temperature	Operating temperature			
	min	°C	-20	
	max	°C	+50	

Dimensions



Wiring diagrams



Connect terminals C and 1 as indicated to power the first module.
If other modules are fitted, the respective terminals must be connected accordingly.

Certifications and compliance

Compliance

CSA C22.2 n° 14

IEC/EN 60947-1

IEC/EN 60947-5-1

UL508

Certificates

cULus

EAC

ETIM classification

ETIM 8.0

EC000232 -
Optical module
for signal tower