



Enclosed
automatic
transfer switches
ATPEP031N00

Product designation

Product type designation

AC Power supply

Rated supply voltage AC VAC 230

Current inputs

Rated current (Ie) A 16

Ambient conditions

Temperature

Operating temperature

min	°C	-5
max	°C	55

Max altitude m 3000

Housing

Weight g 2100

Certifications and compliance

Compliance

EN61439-2

Certificates

/