



Enclosed  
automatic  
transfer switches  
ATPEP031N00

Product designation

Product type designation

**AC Power supply**

Rated supply voltage AC VAC 230

**Current inputs**

Rated current (Ie) A 16

**Ambient conditions**

Temperature

Operating temperature

|     |    |    |
|-----|----|----|
| min | °C | -5 |
| max | °C | 55 |

Max altitude m 3000

**Housing**

Weight g 2100

**Certifications and compliance**

Compliance

EN61439-2

Certificates

/