



Enclosed
automatic
transfer switches

Product designation

AC Power supply			
Rated supply voltage AC	VAC	400	
Current inputs			
Rated current (Ie)	A	30	
Ambient conditions			
Temperature	Operating temperature		
		min	°C
		max	°C
			-5
			55
Max altitude	m	3000	
Housing			
Weight	g	7900	
Certifications and compliance			
Compliance	EN61439-2		
Certificates	/		