



Product designation
Product type designation

SOCKET
HR1XS024

Contact characteristics

Rated insulation voltage U_i IEC/EN	V	250
Rated impulse withstand voltage U_{imp}	kV	4

Coil characteristics

Relay control voltage + socket	V	12...24VAC/DC
--------------------------------	---	---------------

Mechanical features

Socket screw tightening tool (cross / flat blade)	Phillips 0/3.5mm
Conductor section	

AWG/Kcmil

min	20
max	16


IEC

min	mm ²	0.5
max	mm ²	1.5


Fixing

On 35mm DIN
rail

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 61810

Certificates

CSA

cURus

EAC

ETIM classification

ETIM 8.0

EC001456 -
Relay socket