



Contact elements
- with mountin
adapter
LPXE

Product designation

Product type designation

Operations

Electrical life	cycles	1000000
-----------------	--------	---------

Mechanical features

Operating force	kg-lb	≤0.5Kg/1.1lb
-----------------	-------	--------------

Tightening torque for terminals max	Nm	1
-------------------------------------	----	---

Terminals screw	Screw
-----------------	-------

Conductor section

AWG/kcmil conductor section

max	14
-----	----

IEC

max	mm ²	1 or 2 / 2.5
-----	-----------------	--------------

Mounting adapter	LPXAU120
------------------	----------

Weight	g	29
--------	---	----

Ambient conditions

Temperature

Operating temperature

min	°C	-25
-----	----	-----

max	°C	+70
-----	----	-----

Storage temperature

min	°C	-40
-----	----	-----

max	°C	+85
-----	----	-----

Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 14

IEC/EN/BS 60947-1

IEC/EN/BS 60947-5-1

UL508

Certificates

CCC

cULus

EAC

RINA

ETIM classification

ETIM 8.0

EC002498 -
Accessories/spare
parts for low-
voltage switch
technology