



Product designation

LED elements
steady light
LPXLE

Product type designation

General characteristics

Colour Green

Electrical characteristics

Supply voltage (AC) V 12...30

Supply voltage (DC) V 12...30

Operations

Electrical life hours 100000

Mechanical features

Tightening torque for terminals max Nm 1

Conductor section

AWG/kcmil conductor section

max 12

IEC

max mm² 1 or 2 / 2.5

Mounting adapter

LPXAU120

Weight

g 16

Ambient conditions

Temperature

Operating temperature

min °C -25


max °C +60

Storage temperature


min °C -40

max °C +85

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 14

IEC/EN/BS 60947-1

IEC/EN/BS 60947-5-1

UL508

Certificates

CCC

cULus

EAC

RINA

UL

ETIM classification

ETIM 8.0

EC000204 -
Lamp holder
block for control
circuit devices