



Automatic transfer switch controller for 2 power sources and one tie-breaker, three phase control, with LCD display, built-in RS485, expandable ATL800

Product designation

Product type designation

General characteristics

Number of controlled power sources	Nr.	2
Number of tie-breaker controlled	Nr.	1
Display		Backlit LCD graphic display 128x80 pixel
Languages	Nr.	8
Expandability		3 expansion slot for EXP... Modules

AC Power supply

Rated supply voltage AC	VAC	110...240
Operating supply voltage range AC	VAC	90...264
Rated frequency	Hz	50/60
Operating frequency range	Hz	45...66
Immunity time for microbreakings		
	110VAC	ms ≤40
	220VAC	ms ≤200

Immunity time for microbreakings (with EXP expansions)

	110VAC 220VAC	ms ms	≤20 ≤100
Power consumption AC (Max)	VA		12.5

DC Power supply

Rated supply voltage DC	VDC	12-24-48
Operating supply voltage range DC	VDC	7.5...57.6
Current consumption Max	mA	400mA at 12VDC, 220mA at 24VDC, 100mA at 48VDC
Maximum power consumption / dissipation	W	4.8

Voltage inputs

Maximum rated voltage Ue		100...600VAC L-L (346VAC L-N)
Measurement range	V	50...720VAC L-L (415VAC L-N)
Frequency range	Hz	45...66

Measurement method		True root mean square (TRMS)
Input impedance	phase-phase phase-neutral	>1.10MΩ >0.55MΩ
Measuring accuracy		±0.25% f.s. ±1 digit
Wiring mode		Single-phase, two-phase, three-phase line with or without neutral and balanced three-phase system
Digital inputs		
Number of digital input	Nr.	8
Type of digital input		Negative
Digital current inputs	mA	≤8
Low input signal	VDC	≤2.2
High input signal	VDC	≥3.4
Input signal delay	ms	≥50
Calendar clock		
Backup reserve power		Backup capacitor
Operating without power voltage		14 days approximately
Relay outputs		
Number of relay output	Nr.	7
Contact arrangement		4 x 1NO-SPST + 3 x C/O-SPDT
Electrical life	cycles	10 ⁵
Mechanical life	cycles	10 ⁷
Interface		
NFC interf.		Yes
Front optical USB communication port		Yes, with CX01 USB dongle (optional)
Front optical Wi-Fi communication port		Yes, with CX02 Wi-Fi dongle (optional)
USB communication		EXP1010 (optional)
RS232 communication		EXP1011 (optional)
RS485 communication		Built-in or EXP1012 (optional)
Ethernet communication		EXP1013 (optional)
Profibus communication		EXP1014 (optional)
Communication via Modem		EXP1015 (optional)
Functions		
Number of tie breakers that can be managed		1
Programmable source type		Yes




Closed transition	Yes
Non-priority load management	Yes
PLC logic	Yes
Timer	Yes
System layout available on display	6
Custom system layouts	Yes
User alarms	Yes
Limits	Yes
Event logging	250
Real time clock with backup reserve energy	Yes
Acoustic alarms	Yes
Analogue inputs	EXP1004 (optional)
Analogue outputs	EXP1005 (optional)

Ambient conditions

Temperature				
Operating temperature				
		min	°C	-30
		max	°C	+70
Storage temperature				
		min	°C	-30
		max	°C	+80
Relative humidity			%	<80%
Maximum Pollution degree				2
Overvoltage category				3
Measurement category				III
Climatic sequence				Z/ABDM (IEC/EN 60068-2-61)
Shock resistance				15g (IEC/EN 60068-2-27)
Vibration resistance				0.7g (IEC/EN 60058-2-6)
Housing				
Execution				Flush mount
Material				Polycarbonate
Mounting				Flush mount - panel cut-out 220x160 mm
Degree of protection				IP65 on front, IP20 on terminals
Dimensions (W x H x D)		mm		240 x 180 x 43.9
Weight		g		1000


Dimensions

CONMUTADOR AUTOMÁTICO DE REDES CON PUERTO ÓPTICO FRONTAL PARA 2 FUENTES DE ALIMENTACIÓN Y 1 DISYUNTOR (180X240MM), ALIMENTACIÓN 110 ... 240VAC Y 12/24/48VDC, EXPANDIBLE CON MÓDULOS DE EXPANSIÓN, RS485 INTEGRADO




Wiring diagrams


Power connection diagrams
Two breakers




Power connection diagrams
Two breakers and a tie breaker



Control connection diagrams
Two breakers



Control connection diagrams
Two breakers and a tie breaker



Certifications and compliance

Compliance

CSA C22.2 n° 14

IEC/EN 60947-1

IEC/EN 60947-6-1

IEC/EN 61000-6-2

IEC/EN 61000-6-4

IEC/EN 61010-1

IEC/EN 61010-2

UL508

Certificates

cULus

EAC

RCM

ETIM classification

ETIM 8.0

EC000236 - PLC
CPU-module