



Product designation

RF82

Product type designation

Motor protection
relay

General characteristics

Number of poles	Nr.	3
Overvoltage category		III
Pollution degree		3
Frontal IP degree		IP20
Type of release		Thermal
Protection fuse		
	gG (IEC)	A 125
	aM (IEC)	A 80
	K5 (UL)	A 200
Phase failure detection		yes
Reset mode		Manual

Power circuit characteristics

Rated insulation voltage U_i IEC/EN	V	690
Rated impulse withstand voltage U_{imp}	kV	8
Rated operational voltage	V	690
Operational frequency	min	Hz 0
	max	Hz 400
Operational current I_e		
	Operational current min	A 46
	Operational current max	A 65
Tripping class		10A
Test Button		yes
Trip indicator		yes

Terminals

type
screw
width
tool

mm

Yoke clamp
M5
9
Phillips 2

Tightening torque for terminals

min Nm 3.9

max Nm 3.9

min lbin 2.88

max lbin 2.88

Conductor section

AWG/kcmil max 2

Auxiliary circuit characteristics

Auxiliary contacts


NO Nr. 1

NC Nr. 1


Auxiliary Rated insulation voltage U_i IEC/EN

V 690

Auxiliary Rated impulse withstand voltage Uimp	kV	6
Auxiliary Rated operational voltage	V	690
Operating current AC15	24V	A 3
	120V	A 3
	240V	A 1.5
	380V	A 0.95
	480V	A 0.75
	500V	A 0.72
	600V	A 0.6
Operating current DC13	125V	A 0.11
	600V	A 0.22
IEC Conventional free air thermal current Ith	A	10
Terminals	Auxiliary circuit type	screw and washer
	Auxiliary circuit screw	M3,5
	Auxiliary circuit width	mm 8
	Auxiliary circuit tool	Phillips 1
Conductor section	Auxiliary circuit Flexible w/o lug max	mm ² 2.5
	Auxiliary circuit Flexible c/w lug max	mm ² 2.5
Tightening torque for terminals	Auxiliary circuit min	Nm 1
	Auxiliary circuit max	Nm 1
	Auxiliary circuit min	lbin 0.74
	Auxiliary circuit max	lbin 0.74
UL/CSA and IEC/EN 60947-5-1 designation		B600-P600
Ambient conditions		
Operating temperature	min	°C -20
	max	°C 55
Storage temperature	min	°C -55
	max	°C 80
Compensation temperature	min	°C -15
	max	°C 55
Max altitude	m	3000
Mechanical features		
Operating position	normal allowable	Vertical plan ±30°
Fixing		Direct mounting on BF40... BF94...
Weight	g	365
UL technical data		
Full-load current (FLA) for three-phase AC motor	at 480V	A 65
	at 600V	A 65
Dimensions		



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 14

IEC/EN 60947-1

IEC/EN 60947-4-1

UL508

Certifications

cULus

ETIM classification

ETIM 8.0

EC000106 -
Thermal overload
relay