



Enclosed
automatic
transfer switches
ATPBU061N00

Product designation			automatic transfer switches	
Product type designation			ATPBU061N00	
AC Power supply				
Rated supply voltage AC			VAC	230
Current inputs				
Rated current (Ie)			A	25
Ambient conditions				
Temperature				
Operating temperature		min	°C	*5
		max	°C	55
Max altitude			m	3000
Housing				
Weight			g	5400
Certifications and compliance				
Compliance				
EN61439-2				
Certificates				
/				