



Product designation  
Product type designation

SOCKET  
HR1XS110

#### Contact characteristics

Rated insulation voltage $U_i$ IEC/EN	V	250
Rated impulse withstand voltage $U_{imp}$	kV	4

#### Coil characteristics

Relay control voltage + socket	V	110... 125VAC/DC
--------------------------------	---	---------------------

#### Mechanical features

Socket screw tightening tool (cross / flat blade)	Phillips 0/3.5mm
---	------------------

Conductor section

AWG/Kcmil

min	20
max	16


IEC

min	mm <sup>2</sup>	0.5
max	mm <sup>2</sup>	1.5


Fixing

On 35mm DIN  
rail

#### Dimensions



#### Wiring diagrams



#### Certifications and compliance

##### Compliance

IEC/EN 61810

##### Certificates

CSA

cURus

EAC

#### ETIM classification

ETIM 8.0

EC001456 -  
Relay socket