





Product designation				SOCKET	
Product type designation				HR5XS21S	
Contact characteristics					
Rated insulation voltage Ui IEC/EN				V	250
Rated impulse withstand voltage Uimp				kV	4
Mechanical features					
Socket screw tightening tool (cross / flat blade)				Phillips 1/4.5mm	
Conductor section					
AWG/Kcmil					
		min		20	
		max		14	
IEC					
		min		mm²	0.5
		max		mm²	2.5
Fixing				On 35mm DIN rail	

Dimensions



A: 60mm (2.36") with HR3X88
70mm (2.75") with XR5X88

Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 61810

Certificates

CSA

cURus

EAC

ETIM classification

ETIM 8.0

EC001456 -
Relay socket