



Product designation

Product type designation

Signal tower
Ø70mm/2.75"
8LT7C -
Connection
modules

General characteristics

Diameter	mm - inch	70 / 2.75
Colour		Black
IEC degree of protection		IP65

Mechanical features

Tightening torque for terminals max	Nm	0.5
Terminals screw		Screw clamp terminals

Conductor section

AWG/Kcmil

max 16

IEC

max mm² 1.5
g 110

Weight


Ambient conditions

Temperature


Operating temperature

min °C -20
max °C +50

Dimensions



Wiring diagrams



BULB


Connect terminals C and 1 as indicated to power the first module.
If other modules are fitted, the respective terminals must be connected accordingly.

Certifications and compliance

Compliance

CSA C22.2 n°14

IEC/EN 60947-1

IEC/EN 60947-5-1

UL508

Certificates

cULus

EAC

ETIM classification

ETIM 8.0

EC001152 -
Connection
module for signal
tower