




Product designation			Bus module for EASY BRANCH		
Product type designation			EXS0000		
Auxiliary supply Us					
Auxiliary rated supply voltage DC			VDC	24	
Auxiliary operating voltage range DC			min	VDC	20.4
			Max	VDC	27.6
			Power dissipation Max		W
Mechanical features					
Housing type			Polyamide		
Terminals type			Screw		
Conductor cross section			min	mm²	0.2
			Max	mm²	2.5
			min	AWG	12
			Max	AWG	24
Tightening torque (Max)				Nm	0.5
				lbin	4.5
Weight			g	90	
Ambient conditions					
Temperature			Operating temperature		
			min	°C	-20
			max	°C	+60
			Storage temperature		
			min	°C	-30
			max	°C	+80
Relative humidity			%	<80	
Maximum Pollution degree					2
Overvoltage category					3
Protection degree					IP20
Dimensions					



Certifications and compliance

Compliance

IEC/EN/BS 61000-6-2

IEC/EN/BS 61000-6-4

IEC/EN/BS 61010-1

Certificates

CE

EAC

UKCA