



Selector switch  
actuators lever -  
2 position  
LPSS12

## Product designation

## Product type designation

## General characteristics

Colour	Black
Type of positions	Selector switch
Material	Aluminium and zinc alloy
IEC degree of protection	IP66, IP67 and IP69K

## Mechanical features

Mechanical life	cycles	1000000
Fixing	Without mounting adapter	
Mounting adapter	LPXAU120M	

## UL technical data

UL degree of protection	Type1, 2, 3R, 4, 4X, 12, 12K
-------------------------	------------------------------

## Ambient conditions

### Temperature


#### Operating temperature

min	°C	-25
max	°C	+70

#### Storage temperature

min	°C	-40
max	°C	+85

## Dimensions



## Certifications and compliance

### Compliance

CSA C22.2 n° 14
IEC/EN/BS 60947-1
IEC/EN/BS 60947-5-1
UL508

### Certificates

cULus

## ETIM classification

ETIM 8.0

EC002611 -  
Control switch