



Product designation				Protocol converter		
Product type designation				EXCCON02		
General characteristics						
Description				RS485-Ethernet Modbus protocol converter		
Functions				RS485/Ethernet		
Rated power supply voltage				9...48VDC, 24VAC		
Communications						
Type of communication port				RS485/Ethernet		
Protocols supported				Modbus, Serial device TCP server/client		
Monitoring method						
Transmission technology				Ethernet/TCP		
Device setup and supervision				Webserver		
Interface						
RS232 communication				Yes		
RS485 communication				Yes		
Ethernet communication				Yes		
Mobile communication				No		
Mechanical features						
Fixing				DIN rail or rear mounting		
Weight			g	430		
Ambient conditions						
Temperature						
Operating temperature				min	°C	-40
				max	°C	+75
Certifications and compliance						
Certifications						
		IEC/EN/BS 55024				
		IEC/EN/BS 55032				
		IEC/EN/BS 55035				
Compliance						
		EAC				
		UCKA				
ETIM classification						
EC000066 - Power contactor, AC switching						