



Enclosed
automatic
transfer switches
ATPBU061N00

Product designation

Product type designation

AC Power supply

Rated supply voltage AC	VAC	230
-------------------------	-----	-----

Current inputs

Rated current (Ie)	A	25
--------------------	---	----

Ambient conditions

Temperature	Operating temperature			
		min	°C	*5
		max	°C	55
Max altitude		m		3000

Housing

Weight	g	5400
--------	---	------

Certifications and compliance

Compliance	EN61439-2
------------	-----------

Certificates	/
--------------	---