



Product designation				Protocol converter	
Product type designation				EXCCON02	
General characteristics					
Description				RS485-Ethernet Modbus protocol converter	
Functions				RS485/Ethernet	
Rated power supply voltage				9...48VDC, 24VAC	
Communications					
Type of communication port				RS485/Ethernet	
Protocols supported				Modbus, Serial device TCP server/client	
Monitoring method					
Transmission technology				Ethernet/TCP	
Device setup and supervision				Webserver	
Interface					
RS232 communication				Yes	
RS485 communication				Yes	
Ethernet communication				Yes	
Mobile communication				No	
Mechanical features					
Fixing				DIN rail or rear mounting	
Weight				g	430
Ambient conditions					
Temperature					
Operating temperature				min	°C
				max	°C
					-40
					+75
Certifications and compliance					
Certifications					
		IEC/EN/BS 55024			
		IEC/EN/BS 55032			
		IEC/EN/BS 55035			
Compliance					
		EAC			
		UCKA			
ETIM classification					
EC000066 - Power contactor, AC switching					