



Product designation

Reversing  
contactor  
BGTP09

Product type designation

#### Electrical features

Maximum operating current ( $\leq 440V$ )

A 9

#### Contact characteristics

Operational current  $I_e$

AC-3 ( $\leq 440V \leq 55^\circ C$ ) A 9

Rated operational power AC-3 ( $T \leq 55^\circ C$ )

230V	kW	2.2
400V	kW	4
415V	kW	4.3
440V	kW	4.5
500V	kW	5

Built-in auxiliary contacts

NO	0
NC	1

#### UL technical data

Maximum UL/CSA horsepower ratings single-phase

110V-120V	HP	0.5
220V-240V	HP	1.5

Maximum UL/CSA horsepower ratings three-phase, 3-pole

200V-208V	HP	2
220V-240V	HP	3
440V-480V	HP	5

#### Mechanical features


Terminals type

Clamp screw


Weight

g 400

#### Dimensions



#### Wiring diagrams



### Certifications and compliance

#### Compliance

IEC/EN 60947-1

IEC/EN 60947-4-1

UL508 CSA C22.2 n° 14

#### Certificates

cULus

### ETIM classification

ETIM 8.0

EC001037 -  
Motor  
starter/Motor  
starter  
combination