




Product designation	AUXILIARY CONTACTS		
Product type designation	CN		
Number of DIN modules	0.5		
Electrical features			
IEC Conventional free air thermal current Ith	A	6	
Rated insulation voltage Ui IEC/EN	V	500	
Rated impulse withstand voltage Uimp	kV	4	
Minimum switching capacity	≥12V ≥5mA		
Control circuit			
Auxiliary contacts	NO	Nr.	1
	NC	Nr.	1
Operations			
Mechanical life	cycles		3000000
Ambient conditions			
Operating temperature	min	°C	-5
	max	°C	55
Storage temperature	min	°C	-30
	max	°C	80
Max altitude	m		2000
Mechanical features			
Tightening torque for terminals	max	Nm	0.8
Terminals tool	PZ2		
Weight	g		44
Resistance & Protection			
Pollution degree	3		
Dimensions			



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 60947-1

IEC/EN 60947-4-1

IEC/EN 60947-5-1

IEC/EN 61095

Certificates

EAC

ETIM classification

ETIM 8.0

EC000041 -
Auxiliary contact
block