



Product designation	Time relay		
Product type designation	TMM1NFC		
Number of DIN modules	1		
General characteristics			
Description	Multifunction time relay, programmable with NFC, multiscale and multivoltage		
Function	Multifunction		
Supply circuit			
Rated auxiliary supply voltage U_s	12...240VAC/DC		
Rated auxiliary supply voltage U_s AC	min	VAC	12
	Max	VAC	240
DC	min	VDC	12
	Max	VDC	240
Rated frequency	Hz		50/60
Operating voltage range	0.85...1.1 U_s		
Maximum power consumption / dissipation	W		0.6VA/0.3W (12...48VAC/DC), 1.6VA/1.2W (110...240VAC/DC)
Immunity time for microbreakings	ms		≤25
Timing circuit			
Time setting range	0.1s...999days		
Repeat accuracy	%		<±0.1
Influence of voltage variation	%		<±0.1
Influence of temperature variation	%		<±0.2
External command input	Minimum ON time	ms	25
	Connenction time		permanent
Resetting time	During timing	ms	≥100
	Elapsed time	ms	≥50
Relay outputs			
Number of relays	Nr.		1
Contact arrangement	1 delayed changeover		
Maximum switching voltage	VAC		250
IEC Conventional free air thermal current I_{th}	A		8
UL/CSA and IEC/EN 60947-5-1 designation	B300		
Insulation (input-output)			

Rated insulation voltage U_i	V	250
Rated impulse withstand voltage U_{imp}	kV	4
Power frequency withstand voltage	kV	2

Connections

Terminals type	Screw		
Tightening torque (Max)	Tightening torque Max	Nm	0.8
	Tightening torque Max	Ibin	7 / 7...9 UL

Conductor section	AWG/Kcmil	min	max	24...12	12...18
	IEC	min	max	mm ²	mm ²
				0.2	4

Operations

Mechanical life	cycles	30000000
Electrical life (with rated load)	cycles	100000


Ambient conditions

Temperature	Operating temperature	min	max	°C	°C	-20	+60
	Storage temperature	min	max	°C	°C	-30	+80
Relative humidity				%		<90%	
Maximum Pollution degree						2	
Overvoltage category						III	


Housing

Execution (n° of modules)	1
Material	Self-extinguishing polyamide
Mounting	DIN rail 35 mm
Degree of protection	IP40 on front, IP20 terminals
Dimensions (W x H x D)	mm17.5 x 104.7 x 64.9
Weight	g86

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n°14

IEC/EN 61812-1

UL508

Certificates

CCC

cULus

EAC

ETIM classification

ETIM 8.0

EC001439 -
Timer relay