
11SN1

SINGLE-POLE ELECTRODE, 100MM/3,94”



Product designation			Probe
Product type designation			SN1
Connections			
Terminals type			Screw
Conductor cross section			
IEC			
	Max	mm²	2.5
Ambient conditions			
Temperature			
Operating temperature			
	max	°C	+60
Housing			
Weight		g	50
Dimensions [mm (in)]			



Certifications and compliance	
Compliance	
/	
Certificates	
EAC	
ETIM classification	
ETIM 8.0	EC001447 - (Fill) level monitoring relay

The characteristics described in this document are subject to updates or modifications at any time. The descriptions, technical and functional information, illustrations and instructions in this brochure are purely illustrative, and are consequently not contractually binding