
8LT7EL4


STEADY LIGHT MODULE. Ø70MM BA15D FITTING, DIRECT SUPPLY, RED



Product designation			Signal tower Ø70mm/2.75"
Product type designation			8TL7EL - Light mudules
General characteristics			
Diameter		mm - inch	70 / 2.75
Supply voltage (DC)		V	24
Colour			Red
IEC degree of protection			IP65
Mechanical features			
Weight		g	82
Ambient conditions			
Temperature			
Operating temperature			
	min	°C	-20
	max	°C	+50

Dimensions [mm (in)]






The characteristics described in this document are subject to updates or modifications at any time. The descriptions, technical and functional information, illustrations and instructions in this brochure are purely illustrative, and are consequently not contractually binding

8LT7EL4

STEADY LIGHT MODULE. Ø70MM BA15D FITTING, DIRECT SUPPLY, RED

Wiring diagrams



Connect terminals C and 1 as indicated to power the first module.
If other modules are fitted, the respective terminals must be connected accordingly.

Certifications and compliance

Compliance

CSA C22.2 n° 14
IEC/EN 60947-1
IEC/EN 60947-5-1
UL508

Certificates

cULus
EAC

ETIM classification

ETIM 8.0	EC000232 - Optical module for signal tower

The characteristics described in this document are subject to updates or modifications at any time. The descriptions, technical and functional information, illustrations and instructions in this brochure are purely illustrative, and are consequently not contractually binding