





Product designation			Power contactor
Product type designation			B1600
Contact characteristics			
Number of poles		Nr.	3
Rated insulation voltage Ui IEC/EN		V	690
Rated impulse withstand voltage Uimp		kV	8
Operational frequency		min	Hz
		max	Hz
IEC Conventional free air thermal current Ith		A	1600
Operational current Ie		AC-1 (≤40°C)	A
		AC-1 (≤55°C)	A
		AC-1 (≤70°C)	A
Rated operational power AC-1 (T≤40°C)		230V	kW
		400V	kW
		500V	kW
		690V	kW
Short-time allowable current for 10s (IEC/EN60947-1)		A	8300
Protection fuse		gG (IEC)	A
			A
Making capacity (RMS value)		A	6300
Breaking capacity at voltage		440V	A
		500V	A
		690V	A
Resistance per pole (average value)		mΩ	7
Power dissipation per pole (average value)		Ith	W
Tightening torque for terminals		min	Nm
		max	Nm
		min	lbin
		max	lbin
Max number of wires simultaneously connectable		Nr.	2
Power terminal protection according to IEC/EN 60529			IP00
Mechanical features			
Operating position		normal	Vertical plan
		allowable	±30°
Fixing			Screw
Weight		g	4915
Auxiliary contact characteristics			
Thermal current Ith		A	16

IEC/EN 60947-5-1 designation		A600 - P600	
Operating current AC15		230V	A 3
		400V	A 1.9
		500V	A 1.4
Operating current DC12		110V	A 5.7
Operating current DC13		24V	A 5.7
		48V	A 2.9
		60V	A 2.3
		125V	A 0.6
		220V	A 0.2
		600V	A 1.2
Operations			
Mechanical life		cycles	5000000
Electrical life		cycles	700000
Safety related data			
Performance level B10d according to EN/ISO 13489-1			
		rated load	cycles 700000
		mechanical load	cycles 5000000
Mirror contacts according to IEC/EN 60947-4-1			yes
EMC compatibility			yes
AC coil operating			
Rated AC voltage at 50/60Hz, 60Hz			
		min	V 220
		max	V 240
AC operating voltage			
of 50/60Hz coil powered at 50Hz			
pick-up		min	%Us 80
		max	%Us 110
drop-out		min	%Us 20
		max	%Us 60
of 50/60Hz coil powered at 60Hz			
pick-up		min	%Us 80
		max	%Us 110
drop-out		min	%Us 20
		max	%Us 60
of 60Hz coil powered at 60Hz			
pick-up		min	%Us 80
		max	%Us 110
drop-out		min	%Us 20
		max	%Us 60
AC average coil consumption at 20°C			
of 50/60Hz coil powered at 50Hz		in-rush	VA 800
		holding	VA 45
of 50/60Hz coil powered at 60Hz			

		in-rush holding	VA VA	800 45
Dissipation at holding ≤20°C 50Hz			W	40
DC coil operating				
DC rated control voltage		min max	V V	220 240
DC operating voltage				
	pick-up			
		min	%Us	80
Max cycles frequency				
Mechanical operation			cycles/h	1200
Operating times				
Average time for Us control				
	in AC			
		Closing NO		
		min	ms	300
		max	ms	450
		Opening NO		
		min	ms	70
		max	ms	130
	in DC			
		Closing NO		
		min	ms	300
		max	ms	450
		Opening NO		
		min	ms	70
		max	ms	130
UL technical data				
Contact rating of auxiliary contacts according to UL				A600 - P600
Ambient conditions				
Temperature				
	Operating temperature			
		min	°C	-50
		max	°C	60
	Storage temperature			
		min	°C	-60
		max	°C	80
Max altitude			m	3000
Resistance & Protection				
Pollution degree				3
Dimensions				



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 60947-1

CSA C22.2 n° 60947-4-1

IEC/EN 60947-1

IEC/EN 60947-4-1

UL 60947-1

UL 60947-4-1

Certificates

/

ETIM classification

ETIM 8.0

EC000066 -
Power contactor,
AC switching