



Product designation Power distribution block

Electrical features

Number of poles	1
Rated insulation voltage Ui	V 1000
IEC Conventional free air thermal current Ith	A 520
Rated peak withstand current Ipk	kA 51
Rated short time current Icw 60s	A 24.5

Connections

Terminal hole diameter_Option 1	mm	Slot 25x9.5mm
Conductor section connectable_Option 1	mm2	flexible busbar 25x9.5mm
Terminal hole diameter_Option 2	mm	2x9,5mm
Conductor section connectable_Option 2	mm2	6...25
Terminal hole diameter_Option 3	mm	5x7mm
Conductor section connectable_Option 3	mm2	2,5...16


Mechanical features

Operating position	normal allowable	Vertical plane Any
Fixing		Screw / DIN rail 35mm
Metric Allen Key	mm	3-4-5
Weight	g	393

Resistance & Protection

Terminals IP degree	IP20 front
---------------------	------------

Dimensions



Certifications and compliance

Certifications

IEC/EN/BS 60947-7-1

Compliance

cURus

ETIM classification

EC000066 - Power contactor, AC switching