



| AC coil operating                   |  |  |                                 |         |
|-------------------------------------|--|--|---------------------------------|---------|
| Rated AC voltage at 60Hz            |  |  | V                               | 460     |
| AC operating voltage                |  |  |                                 |         |
| of 60Hz coil powered at 60Hz        |  |  |                                 |         |
| pick-up                             |  |  | min                             | %Us 80  |
|                                     |  |  | max                             | %Us 110 |
| drop-out                            |  |  | min                             | %Us 20  |
|                                     |  |  | max                             | %Us 55  |
| AC average coil consumption at 20°C |  |  |                                 |         |
| of 60Hz coil powered at 60Hz        |  |  |                                 |         |
|                                     |  |  | in-rush                         | VA 75   |
|                                     |  |  | holding                         | VA 9    |
| Dissipation at holding ≤20°C 50Hz   |  |  | W                               | 2.5     |
| Certifications and compliance       |  |  |                                 |         |
| Certificates                        |  |  |                                 |         |
| /                                   |  |  |                                 |         |
| ETIM classification                 |  |  |                                 |         |
| ETIM 8.0                            |  |  | EC002563 - Coil for low-voltage |         |