



Product designation

MINIATURE
RELAYS
HR401C

Product type designation

Contact characteristics

Contact configuration			1 C/O
Rated insulation voltage U_i IEC/EN	V		250
Rated impulse withstand voltage U_{imp}	kV		4
IEC Conventional free air thermal current I_{th}	A		16
Maximum instantaneous current	A		60
Rated current (I_n)	A		16
Relay control voltage	V		12VDC

Max contrrollable power in

AC-1	W	3840
AC-15	VA	150

Rated operating power AC-1

VA	4000
----	------

Rated operating power AC-15

230 VAC	VA	500
---------	----	-----

Single-phase motor control

230VAC	kW	0.37
--------	----	------

Rated operating current DC-1

30V	A	10
110V	A	0.3
220V	A	0.12

Minimum switching load

V / mA	5 / 100
--------	---------

Contact impedance

mΩ	100
----	-----

Contact material

AgSnO₂

Operating times

Closing	ms	<15
Opening	ms	<5

Operations

Mechanical life	cycles	10000000
Electrical life AC1	cycles	100000

Coil characteristics

Average coil consumption DC at 20°C	W	0.7
-------------------------------------	---	-----

Operating range

Closing	% U_n	75...110
Opening	% U_n	10...30

Maximum cycle frequency

cycles/h	3600
----------	------

Mechanical features

Max socket terminal tightening torque	Nm	0.6
---------------------------------------	----	-----

Socket screw tightening tool (cross / flat blade)		PH1 / 4.5mm
---	--	-------------

Conductor section

AWG/Kcmil

min	20
-----	----

IEC	max	14	
	min	mm ²	0.5
	max	mm ²	2.5

Operating position	normal	Any
--------------------	--------	-----

Fixing	On 35mm DIN rail and with screw	
--------	---------------------------------	--


Ambient conditions

Temperature		Operating temperature	
	min	°C	-40
	max	°C	+85
		Storage temperature	
	min	°C	-40
	max	°C	+85


Other features

Indication	No
Mechanical contact position indicator	No
Mechanical test actuator	No


Dimensions



PCB layout



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 61810

Certificates

cURus

VDE

ETIM classification

ETIM 8.0

EC001437 –
Switching relay