



Product designation

Product type designation

Number of poles

Operating voltage type

Switch
disconnecter
GA
Nr. 3
AC

Contact characteristics

IEC Conventional free air thermal current I _{th}	A	80
Rated insulation voltage U _i IEC/EN	V	1000
Rated impulse withstand voltage U _{imp}	kV	8

Operating current I_e

AC21A

400V	A	80
500V	A	80
690V	A	80

AC22A

400V	A	80
500V	A	80
690V	A	80

AC23A

400V	A	80
500V	A	63
690V	A	47

Power dissipation per pole max	W	2.6
--------------------------------	---	-----

Rated operational power AC23A

400V	kW	45
690V	kW	45

Rated short time current (1s) I _{cs} (rms)	kA	2.5
---	----	-----

Conditional short-circuit current (rms)	kA	50
---	----	----

Short-circuit protection with fuse	Class/A	gG80
------------------------------------	---------	------

Making capacity AC23A 400V	A	1250
----------------------------	---	------

Breaking capacity AC23A 400V	A	1000
------------------------------	---	------

Mechanical life	cycles	30000
-----------------	--------	-------

Electrical life AC21A	cycles	30000
-----------------------	--------	-------

Mechanical features

Operating position

normal
allowable
Vertical plan
Any

Fixing	By screw on the door
--------	----------------------

Terminals

type	Pillar
width	mm 12.4
height	mm 10.4
screw	M8
tool	Metric Allen key 4

Tightening torque for terminals

min	Nm	5
max	Nm	6
min	lbin	45
max	lbin	54

Conductor section

IEC min	mm ²	4
IEC max	mm ²	70
AWG/kcmil min		12
AWG/kcmil max		1

UL technical data

UL Standard			UL98
General purpose current rating	A		IEC/EN UL98 CSA C22.2 n°4
Operating voltage max	V		IEC/EN UL98 CSA C22.2 n°4
Horsepower/FLA current three phase motor			
	240V	HP	IEC/EN UL98 CSA C22.2 n°4
	480V	HP	IEC/EN UL98 CSA C22.2 n°4
	600V	HP	IEC/EN UL98 CSA C22.2 n°4
Short circuit rating	kA rms		50 (600V) / 100 (480V)
Short circuit rating with fuse	Class/A		J/100A / CC-J-T/max. 200A
Minimum enclosure dimensions at rated current	mm in	mm in	150x140x110 5.9 x 5.5 x 4.3


Ambient conditions

Operating temperature	min max	°C °C	-25 +55
Storage temperature	min max	°C °C	-40 +70
Max altitude		m	3000


Resistance & Protection

Frontal IP degree		IP20
Pollution degree		3

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n°4

IEC/EN 60947-1

IEC/EN 60947-3

UL98

Certifications

CCC

CSA C22.2 n°4

cULus according to UL98

EAC

ETIM classification

ETIM 8.0

EC000216 -
Switch
disconnecter