





Product designation			Monoblock potentiometers
Product type designation			LPCPA
General characteristics			
Type of positions			Potentiometer
Resistance value		KΩ	10
Material			Polyamide - Resistive material: cermet
IEC degree of protection			IP66, IP67; IP96K on front and IP20 on rear
Electrical characteristics			
Rated insulation voltage Ui IEC/EN		V	250VAC
Rated impulse withstand voltage Uimp		kV	4
Max power		W	1
Mechanical features			
Mechanical travel		°	290
Weight		g	40
UL technical data			
UL degree of protection			1, 2, 3R, 4, 4X, 12, 12K on front
Ambient conditions			
Temperature			
Operating temperature			
	min	°C	-25
	max	°C	+70
Storage temperature			
	min	°C	-40
	max	°C	+85
Resistance & Protection			
Resistance tolerance		%	±10%
Dimensions			



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 14
IEC/EN/BS 60947-1
IEC/EN/BS 60947-5-1
UL508

Certificates

CCC
cULus
EAC

ETIM classification

ETIM 8.0

EC001027 -
Potentiometer for
command
devices