



Monoblock buzzer  
- Continuous or  
pulse tone  
LPCZS

Product designation

Product type designation

#### General characteristics

Type of positions	Buzzer
Material	Polyamide
IEC degree of protection	IP66, IP67; IP96K on front and IP20 on rear

#### Electrical characteristics

Rated impulse withstand voltage Uimp	kV	4
Rated frequency	Hz	50-60
Supply voltage (AC)	V	85...140
Supply voltage (DC)	V	85...140

#### Mechanical features

Tightening torque for terminals max	Nm	0.5
Screwdriver	Flat-head:	0.6x3.5mm/0.02x0.
Conductor section		

AWG/kcmil conductor section

min	24
max	14

IEC

min	mm <sup>2</sup>	0.5
max	mm <sup>2</sup>	2.5

Weight	g	20
--------	---	----

#### UL technical data

UL degree of protection	1, 2, 3R, 4, 4X, 12, 12K on front
-------------------------	--------------------------------------

#### Ambient conditions

Temperature


Operating temperature

min	°C	-25
max	°C	+70


Storage temperature

min	°C	-40
max	°C	+85

#### Dimensions



## Wiring diagrams



## Certifications and compliance

### Compliance

CSA C22.2 n° 14

IEC/EN/BS 60947-1

IEC/EN/BS 60947-5-1

UL508

### Certificates

CCC

cULus

EAC

## ETIM classification

ETIM 8.0

EC000130 -  
Signal horn