




Product designation			Joystick		
Product type designation			LPSJ		
General characteristics					
Type of positions			Joystick		
Material			Aluminium and zinc alloy for metal parts and polyamide for plastic parts. Sealing boot is NBR rubber		
IEC degree of protection			IP66, IP67 and IP69K		
Electrical characteristics					
Rated insulation voltage Ui IEC/EN			V	690	
IEC Conventional free air thermal current Ith			A	10	
UL/CSA and IEC/EN 60947-5-1 designation			A300 Q300		
Operating current AC15			12V	A	6
			24V	A	6
			48V	A	6
			120V	A	6
			240V	A	3
			Operating current DC13		
24V	A	0.55			
48V	A	0.55			
125V	A	0.55			
250V	A	0.27			
Contact resistance					
Mechanical features					
Mechanical life			cycles	1000000	
Tightening torque for terminals max			Nm	1	
Terminals screw			Clamp screw with washer		
Mounting adapter			Included with contacts		
UL technical data					
UL degree of protection			Type 1, 2, 3R, 4, 4X, 12, 12K		
Ambient conditions					
Temperature			Operating temperature		
			min	°C	-25
			max	°C	+60
Storage temperature					

min	°C	-40
max	°C	+70

Dimensions



Certifications and compliance

Compliance

CSA C22.2 n° 14
IEC/EN/BS 60947-1
IEC/EN/BS 60947-5-1
UL508

Certificates

cULus

ETIM classification

ETIM 8.0

EC000632 -  
Control switch,  
Joystick