



LED elements
steady light base
mount on LPZ
control station
LPXLPB

Product designation

Product type designation

General characteristics

Colour Green

Electrical characteristics

Rated frequency	Hz	50-60
Supply voltage (AC)	V	85...140

Operations

Electrical life	hours	100000
-----------------	-------	--------

Mechanical features

Conductor section

AWG/kcmil conductor section

max	14
-----	----

IEC

max	mm ²	1 or 2 / 2.5
-----	-----------------	--------------

Mounting adapter	LPXAU120
------------------	----------

Weight	g	16
--------	---	----

Ambient conditions

Temperature

Operating temperature


min	°C	-25
max	°C	+70

Storage temperature


min	°C	-40
max	°C	+85

Dimensions

Mounting position on the LPZ control station base



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 14
IEC/EN/BS 60947-1
IEC/EN/BS 60947-5-1
UL508

Certificates

CCC
cULus
EAC
RINA
UL

ETIM classification

ETIM 8.0

EC000204 -
Lamp holder
block for control
circuit devices