





Product designation		Top roller push plunger	
Product type designation		KPB1	
General characteristics			
Material		Housing	Aluminium-zinc alloy
		Roller	Plastic
Contact characteristics			
Type of contact		1NO+1NC Slow action	
Thermal current Ith		A	10
IEC/EN 60947-5-1 designation		B300 R300	
Rated insulation voltage Ui		V	400
Rated impulse withstand voltage Uimp		kV	4
Insulation class		I	
IEC Conventional free air thermal current Ith		A	10
Resistance per pole (average value)		mΩ	<25
Conductivity		10mA 5V	
Mechanical features			
Operating head fixing		Fixed	
Operating torque		N	10
		lb	2.2
Tightening torque (Max)			
Switch fixing		Nm	2.5
		lbin	22.1
Weight		g	290
Operations			
Mechanical life		cycles	>10000000
Mechanical operation		cycles/h	3600
Ambient conditions			
Temperature			
Operating temperature		min	°C -25
		max	°C +70
Storage temperature		min	°C -40
		max	°C +70
Resistance & Protection			
IP degree		Body housing	IP67
Pollution degree		3	
Dimensions			



Wiring diagrams

Slow action



1NO + 1NC

Certifications and compliance

Compliance

CSA C22.2 n° 14.

IEC/EN 60947-1

IEC/EN 60947-5-1

UL508

Certificates

cULus

EAC

ETIM classification

ETIM 8.0

EC000030 - End
switch