



LED elements  
steady light base  
mount on LPZ  
control station  
LPXLPB

Product designation

Product type designation

#### General characteristics

Colour Red

#### Electrical characteristics

Rated frequency	Hz	50-60
Supply voltage (AC)	V	85...140

#### Operations

Electrical life	hours	100000
-----------------	-------	--------

#### Mechanical features

Conductor section

AWG/kcmil conductor section

max	14
-----	----

IEC

max	mm <sup>2</sup>	1 or 2 / 2.5
-----	-----------------	--------------

Mounting adapter	LPXAU120
------------------	----------

Weight	g	16
--------	---	----

#### Ambient conditions

Temperature

Operating temperature


min	°C	-25
max	°C	+70

Storage temperature


min	°C	-40
max	°C	+85

#### Dimensions

### Mounting position on the LPZ control station base



### Wiring diagrams



### Certifications and compliance

#### Compliance

CSA C22.2 n° 14  
IEC/EN/BS 60947-1  
IEC/EN/BS 60947-5-1  
UL508

#### Certificates

CCC  
cULus  
EAC  
RINA  
UL

### ETIM classification

ETIM 8.0

EC000204 -  
Lamp holder  
block for control  
circuit devices