





Product designation			Direct-on-line starter
Product type designation			M0P00912...2V3
Electrical features			
Relay adj range	A	1.4-2.3	
IEC technical characteristics (≤440V)	Ie kW	A kW	2.3 0.55...0.75
Components			
Starter enclosure standard supplied			M0PA
Contactor standard supplied			BG0910A
Thermal relay standard supplied			RF92V3
UL technical data			
Maximum UL/CSA horsepower ratings single-phase	220V-240V	HP	0.5
Maximum UL/CSA horsepower ratings three-phase, 3-pole	440V-480V	HP	1
	550V-600V	HP	1
Mechanical features			
Weight	g	760	
Ambient conditions			
Operating temperature	min	°C	-25
	max	°C	+60
Storage temperature	min	°C	-40
	max	°C	+70
Resistance & Protection			
Frontal IP degree			IP65
Dimensions			



Wiring diagrams



I = Start; O = Stop/Reset

Certifications and compliance

Compliance

IEC/EN 60947-1
IEC/EN 60947-4-1
UL508 CSA C22.2 n° 14

Certificates

CSAus
cULus
EAC

ETIM classification

ETIM 8.0

EC001037 -
Motor
starter/Motor
starter
combination