



Product designation				Switching power supplies
Product type designation				PSL1
Input characteristics				
Input type				Single-phase
Rated supply voltage AC			VAC	Multivoltage 100...240
Operating range				
AC		min	VAC	90
		Max	VAC	264
DC		min	VDC	120
		Max	VDC	375
Rated frequency			Hz	50/60
Operational frequency				
		min	Hz	47
		max	Hz	63
Current consumption Max			mA	2400
Insulation voltage Input/Output				
		AC	VAC	3000
		DC	VAC	4242
Internal fuse (250VAC)				T3 15A
Output characteristics				
Rated output voltage DC			VDC	48
Voltage trimming (potentiometer) DC				
		min	VDC	47
		Max	VDC	56
Rated output current			A	2.1
Rated output power			W	100
Temperature coefficient			%/°C	0.03
Line adjustment			%	±1
Load adjustment			%	±1
Efficiency			%	88
Overload protection				110...140%
Short-circuit protection				Fold forward
Ripple & noise			mV	50
Indications				
LED indicator for power on				Yes
LED indicator for low voltage				Yes
Power Rdy (Ready - minimum limit)				Yes (relay output - 17.6VDC)
Connections				
Terminals type				Screw
Ambient conditions				

Temperature

Operating temperature

min	°C	-35
max	°C	+71

Storage temperature

min	°C	-40
max	°C	+85

Derating	%/°C	2.5
----------	------	-----

Housing

Material	Plastic
----------	---------

IEC degree of protection	IP20
--------------------------	------


Dimensions (W x H x D)	mm	54 x 90 x 115
------------------------	----	---------------

Weight	g	508
--------	---	-----

Installations


Mounting	On 35mm DIN rail
----------	------------------

Dimensions



TYPE	A	B	C
PSL1 005 24	22.5 (0.88")	90 (3.54")	115 (4.53")
PSL1 010 24	22.5 (0.88")	90 (3.54")	115 (4.53")
PSL1 018 24	22.5 (0.88")	90 (3.54")	115 (4.53")
PSL1 030...	40.5 (1.59")	90 (3.54")	115 (4.53")
PSL1 060...	40.5 (1.59")	90 (3.54")	115 (4.53")
PSL1 100...	54 (2.12")	90 (3.54")	115 (4.53")
PSL2 100...	54 (2.12")	90 (3.54")	115 (4.53")
PSLR 20 24	54 (2.12")	90 (3.54")	115 (4.53")

Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n°14
IEC/EN/BS 61000-6-2
IEC/EN/BS 61000-6-3
IEC/EN/BS 62368-1
UL 508

Certificates

cULus
EAC
RCM

ETIM classification

ETIM 8.0

EC002540 - DC-
power supply