




Product designation	Miniature circuit breaker (MCB)		
Product type designation	P1 MB		
Number of poles	1P		
Number of DIN modules	1		
Compliance	IEC / UL489		
Electrical features			
Rated insulation voltage Ui IEC/EN	V	440	
Rated impulse withstand voltage Uimp	kV	4	
Rated operational voltage AC (IEC)	VAC	230/400	
Rated operational voltage AC (UL)	V	277	
Rated operational voltage DC	VDC	60	
Rated frequency	Hz	50/60	
Rated current (In)	A	30	
Tripping curve			C
Short circuit rating (IEC)	kA	10	
Short circuit rating (UL)	kA	10	
Electrical life	cycles	10000	
Power dissipation per pole max	W	2.46	
Ambient conditions			
Operating temperature	min	°C	-40
	max	°C	+70
Storage temperature	min	°C	-40
	max	°C	+80
Max altitude	m		2000
Mechanical features			
Operating position	normal		Vertical plan
			35mm DIN rail
Fixing			
Tightening torque for terminals	min	Nm	1.8
	max	Nm	2
	min	lbin	16
	max	lbin	17.7
Terminals tool	Pz 2		
Conductor section	IEC		
	min	mm²	1
	max	mm²	35
	AWG/Kcmil		
	min		14
	max		6
Mechanical life	cycles		20000

Weight	g	133
Frontal IP degree		IP20
Pollution degree		2

#### Dimensions



#### Wiring diagrams



#### Certifications and compliance

##### Compliance

IEC/EN 60947-2  
UL489

##### Certifications

cULus  
EAC

#### ETIM classification

ETIM 8.0

EC000042 -  
Miniature circuit  
breaker (MCB)